

# Spectralon® Diffuse Reflectance Standards

High Lambertian reflectance over their effective spectral range



## VALUE

Calibrated Spectralon® standards accredited under NVLAP ISO 17025 Lab Code 200951-0

Highly Lambertian

Durable

Chemically inert

## APPLICATIONS

Densitometers

Integrating sphere systems

Optical equipment

Photographic equipment

Reflectometers

Remote sensing instruments

## Accurate


Spectralon® Diffuse Reflectance Standards offer the highest diffuse reflectance values of any known substance. These durable, chemically inert standards can have typical reflectance values ranging from 2% to 99% and are spectrally flat over the UV-VIS-NIR spectrum. All Spectralon materials are optically flat to +/- 4% over the photopic region of the spectrum.

Spectralon® Diffuse Reflectance Standards are Lambertian, with Spectralon® SRM-99 reflectance material being the most Lambertian reflector available for use over the wavelength range from 250 - 2500 nm.

## Consistent

All reflectance calibration tests are performed in the Reflectance Spectroscopy Laboratory at Labsphere. The standards used in these tests are directly traceable to the National Institute of Standards and Technology (NIST).

Spectralon® Diffuse Reflectance Standards are available individually and in sets, consisting of a diffuse white standard and a selection of diffuse gray standards. Each standard is supplied with complete diffuse reflectance data from 250 - 2500, every 50 nm. All standards are housed in a durable delrin holder with a protective cover.



## Hemispherical Spectral Reflectance Factors

# Specifications

Diffuse Reflectance Standards are available in sets of four or eight standards in either 1.25 or 2.00 inch diameters.

A set of four standards includes one each of the following reflectance values: 99%, 75%, 50% and 2%. A set of eight standards includes one each of the following reflectance values: 99%, 80%, 60%, 40%, 20%, 10%, 5% and 2%.

Set Model Number	Standards Included	Part Number	Reflectance Factor	Reflective Area (Inches)	Dimensions (Inches)
<b>RSS-04-010</b>		AS-01163-060			
	SRS-99-010	AS-01160-060	99%	1.25 D	1.50 D x 0.55 H
	SRS-75-010	AS-01160-260	75%	1.25 D	1.50 D x 0.55 H
	SRS-50-010	AS-01160-460	50%	1.25 D	1.50 D x 0.55 H
	SRS-02-010	AS-01161-960	2%	1.25 D	1.50 D x 0.55 H
<b>RSS-04-020</b>		AS-01165-060			
	SRS-99-020	AS-01161-060	99%	2.00 D	2.38 D x 0.60 H
	SRS-75-020	AS-01161-260	75%	2.00 D	2.38 D x 0.60 H
	SRS-50-020	AS-01161-460	50%	2.00 D	2.38 D x 0.60 H
	SRS-02-020	AS-01161-960	2%	2.00 D	2.38 D x 0.60 H
<b>RSS-08-010</b>		AS-01163-160			
	SRS-99-010	AS-01160-060	99%	1.25 D	1.50 D x 0.55 H
	SRS-80-010	AS-01160-160	80%	1.25 D	1.50 D x 0.55 H
	SRS-60-010	AS-01160-360	60%	1.25 D	1.50 D x 0.55 H
	SRS-40-010	AS-01160-560	40%	1.25 D	1.50 D x 0.55 H
	SRS-20-010	AS-01160-660	20%	1.25 D	1.50 D x 0.55 H
	SRS-10-010	AS-01160-760	10%	1.25 D	1.50 D x 0.55 H
	SRS-05-010	AS-01160-860	5%	1.25 D	1.50 D x 0.55 H
	SRS-02-010	AS-01160-960	2%	1.25 D	1.50 D x 0.55 H
<b>RSS-08-020</b>		AS-01165-160			
	SRS-99-020	AS-01161-060	99%	2.00 D	2.38 D x 0.60 H
	SRS-80-020	AS-01161-160	80%	2.00 D	2.38 D x 0.60 H
	SRS-60-020	AS-01161-360	60%	2.00 D	2.38 D x 0.60 H
	SRS-40-020	AS-01161-560	40%	2.00 D	2.38 D x 0.60 H
	SRS-20-020	AS-01161-660	20%	2.00 D	2.38 D x 0.60 H
	SRS-10-020	AS-01161-760	10%	2.00 D	2.38 D x 0.60 H
	SRS-05-020	AS-01161-860	5%	2.00 D	2.38 D x 0.60 H
	SRS-02-020	AS-01161-960	2%	2.00 D	2.38 D x 0.60 H

## Individual Diffuse Reflectance Standard

Diffuse Reflectance Standards are available individually (1.25 or 2.00 inch diameter) in the following reflectance values: 99%, 80%, 75%, 60%, 50%, 40%, 25%, 20%, 10%, 5% and 2%.

## Custom Reflectance Standards

Spectralon Diffuse Reflectance Standards are available on custom order with reflectance properties to meet your specific needs. Please contact our Technical Sales Department for details.

